# ListenEar personal noise dosemeter



The **Listen Ear Personal Noise Dose Meter** is a very compact noise dose meter to wear during a complete working day.

#### ListenEar features:

- View instantaneous noise level and total exposure of the day on LCD display
- Use Mobile Phone application to control and view data
- Battery time 160 hours / 4 working weeks
- Charged using USB
- Complies to international standards: IEC 61672-1, IEC 61252
- Two Simultaneous Dosimeters in one
- Each Dosimeter (in the one unit) can measure DOSE according to pre-set (ISO,OSHA,NIOSH...) or your custom criteria (Exchange Rate, Level, Threshold) for World standards comparisons, in one time recording session.
- Produce a daily report and stats of the work environment by downloading data

- Default 8 hour day, adjustable in menu
- Tamper proof facility
- Low power radio function base station mounting
- Bright LED for dose alarm warning
- Contains A,C and Z-weighting filters to mimic the frequencies heard by the human ear
- Built in or External Microphone
- Calibrated during manufacture
- Data logging Sound / temperature / humidity / movement
- No USB Drivers required to download data
- Class 2 sound level meter
- Includes movement and orientation monitor
- Records Temperature and Relative Humidity

#### ListenEar Unique features:

#### • Anti-Knock & Vibration System:

A major problem encountered with personal noise dosimeters is distinguishing between true audio impulse noise and extraneous mechanical 'tapping' on the personal noise dosimeter casing. The introduction of a Patented Anti-Knock & Vibration System to the ListenEar provides an additional level of accuracy to the final result. The ListenEar can detect and eliminate the mechanical tapping noise, therefore the noise exposure measured and recorded is an actual representation of that environment. Number of detected 'knocks' is recorded and stored in the report file. The Anti-Knock & Vibration System is not active when the External microphone is connected.

## Simulate the effect of wearing ear defenders:

If you wish to use your ListenEar whilst wearing hearing protection, then this is possible by inputting the SNR attenuation figure from the specification of your hearing defender or ear plug into the instrument setup. The ListenEar will take note of the new setting and give exposure readings as if measuring at your ear inside the hearing defender earmuff and not outside in the external environment.

• Motion detection:


This feature monitors the ListenEar motion status. It will detect if the unit is not worn during the recording session. The 'non motion' event will be detected if the unit is stationary for at least 10 seconds. Number of events and summary of 'no motion' time is recorded in the report file.



Norsonic Benelux BVBA Kerkhovenstraat 2 3461 Molenbeek-Wersbeek

www.norsonic.be info@norsonic.be 0032 (0)498/784907 The Listen Ear can be controlled by an android application. The app allows starting and stopping a measurement, displaying the current measurement results and time history graph.





# ListenEar ordering information and optional accessories:

ListenEar	delivered pre-calibrated and with a USB cable to re-charge the internal battery Standard instrument housing colour is grey, can be delivered in black or white upon request
ListenEar optional accessories:	External Microphone with 50cm lead External Microphone with 50cm lead and LED warning indicator External Microphone with 3m lead ListenEar Body strap Internal Microphone Calibrator Adaptor



Norsonic Benelux BVBA Kerkhovenstraat 2 3461 Molenbeek-Wersbeek www.norsonic.be info@norsonic.be 0032 (0)498/784907

## ListenEar specifications:

Certificates and standards	
IEC 61672: 1993	Class 2 Sound Level Meter
IEC 61252: 1993	Personal Sound Exposure Meter
CE mark	Mark Complies with the Directive on low voltage 73/23/CEE and Directive CEM
	89/336/CEE modified by 93/68/CEE
Sound measurement	
Laeq	70dB to 140dB
Lcpeak	140dB
Overload detectof flag	140,1 dB
Resolution	0,1 dB
Frequency weighting	A, C, Z
Time weighting	Fast, Slow
Exposure measurement	
Dose range	0% to 9999%
Exchange Rate	3dB, 4dB, 5dB, 6dB
Criterion Level for 100% Dose	75 to 90dBA (in 5 dB Increments)
Criterion Threshold	none, 80db, 90dB
Simultaneous analysers	up to 2
Ear defender SNR range	5dB to 45dB
Results	LEQ, LEX8h, LAVG, TWA, LMIN, LMAX, Dose (%), Projected Dose (%,8h)
Environmental measurement	
Temperature range	-40°C to +80°C
Temperature resolution	0.1°C
Humidity	0% - 100% RH
Humidity resolution	1% RH
Motion	3 axis, 10s detection time
Memory	8Mbytes. Accessible by micro USB cable using PC - no drivers required
Microphones	
Internal	Pre-polarised condenser microphone
External	as above + proprietary USB interface
Data logging	
Summary	Summary results for the measurement time
File type	reports: *.txt, history: *.csv
Time history Leq	selectable at intervals 1s, 10s, 30s, 1m, 5m or 10m
Time history temp. and humidity	History stored at same interval as above
Time history motion status	History movement / no movement stored at same interval as above
User interface	
Display	LCD, 128x128, backlit for 6s after keypress
Keypad	two multifunction buttons
Other	multicolour 'info LED'
Battery	
Non removable LiPo	Lithium-Polymer 3.7V / 550mAh
Power consumption	2mA (avg), 20mA (max)
Auto power-off	1h (no motion, not recording)
Charging	micro USB, up to 200mA
Operating time	up to 160 hours / 4 working weeks (depending on features enabled)
Dimensions & weight	
Size	(H x W x D) 83mm x 52mm x 15mm (19mm including clip)
Weight	52g
Environmental	
Operating temperature	0°C to +50°C
Operating Humidity	up to 90% RH, non-condensing
Storage temperature	-10°C to +60°C
Storage Humidity	up to 90% RH, non-condensing

All values are typical unless otherwise stated. We reserve the right to change the specifications without prior notice.



Norsonic Benelux BVBA Kerkhovenstraat 2 3461 Molenbeek-Wersbeek ListenEar V2 jan 2020

www.norsonic.be info@norsonic.be 0032 (0)498/784907